Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Extra Heavy Duty SNAPConnect® Receptacles

HUBBELL

Features

- Green LED Power Indicators
- Aesthetic Style Line® decorator design
- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

Ordering Information

Description Specification grade, with Power Indicating LED, Style Line® decorator face.

Device Color Light Almond

Catalog Number 783585248769

SNAP2152LAL

Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Nylon Base **PBT** Contacts **Brass**

Mounting Strap Galvanized steel Auto Self-grounding Staple Stainless steel Mounting Screws Zinc plated steel

Performance

Electrical

Current Interrupting Receptacle certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device


Environmental

Flammability UL 94V-2

Maximum continuous 75°C; minimum -40°C (without Operating Temperature

impact)





Accessories

Wallplate or Weatherproof Cover StyleLine® Decorator Opening

Resources

eCatalog

