Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty Hospital Grade SNAPConnect® Receptacle

Features

- · Audible SNAP, indicates solid connection
- · Reduces installation time
- · Fully insulated design

Ordering Information

Description
Hospital grade, Style Line®
decorator with power
indicating LED

Device Color White **UPC Number** 783585248820

Catalog Number SNAP2172WL

Listings

UL Listed to UL498 File No. E2186 CSA Certified Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Nylon
Base PBT
Power Contacts Brass
Ground Contacts Brass

Mounting Strap Galvanized steel
Automatic Self-grounding Staple Stainless steel
Mounting Screws Zinc plated steel

Performance

Electrical

Current Interrupting Receptacle certified for current interrupting at full

rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

Environmental

Flammability UL 94V-2


Operating Temperature Maximum continuous 75°C; minimum -40°C

(without impact)

HUBBELL







Complementary Products

Wallplate or Weatherproof Cover

StyleLine® Decorator Opening

Online Resources

Customer Sales Drawings eCatalog Installation Instructions

