Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty Hospital Grade SNAPConnect[®] Receptacle

Features

- · Audible SNAP, indicates solid connection
- Reduces installation time
- · Fully insulated design

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Hospital grade, Style Line® decorator with power	Black	783585248660	SNAP2182BKL
indicating LED			

Listings


UL Listed to UL498 File No. E2186 CSA Certified Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Base Power Contacts Ground Contacts Mounting Strap Automatic Self-grounding Staple Mounting Screws Nylon PBT Brass Brass Galvanized steel Stainless steel Zinc plated steel



HUBBELL



Performance

Electrical Current Interrupting

Dielectric Voltage

Mechanical Product Identification

Environmental Flammability Operating Temperature Receptacle certified for current interrupting at full rated current Withstands 2,000V minimum

Ratings are a permanent part of the device

UL 94V-2 Maximum continuous 75°C; minimum -40°C (without impact)



Wallplate or Weatherproof Cover

StyleLine® Decorator Opening

Online Resources

Customer Sales Drawings eCatalog Installation Instructions



Wiring Device-Kellems