

Straight Blade Devices
20A, 125V, 2 Pole, 3 Wire Grounding
Straight and Right Angle Pigtailed Terminal

Features

- Transparent housing to inspect contacts
- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

Ordering Information

Description	Wire Type	UPC	Catalog Number
Right angle, red terminal with 6-inch leads, Emergency, assembled in USA	Stranded	783585531182	SNAP2REM

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596

Specifications

Contact	Brass
Terminal Body	PBT
Wire	#12 AWG, T90 Nylon FT-1, PVC 90°C (min)

Performance

Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Terminal Identification	Terminal Wire Leads- Identified in accordance with UL 498
-------------------------	---

Environmental

Flammability	UL 94V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

HUBBELL



Accessories

Mating Receptacle	Hubbell SNAPConnect® Receptacle
-------------------	---------------------------------

Resources

[eCatalog](#)

