# 20A, 125V, 2 Pole, 3 Wire Grounding Extra Heavy Duty SNAPConnect® Receptacles

# HUBBELL

#### **Features**

- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

### **Ordering Information**

Catalog Number Description **Device Color** 783585247779 SNAP5362A Specification grade, Brown finder groove.

#### Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 **NEMA® WD-6 Compliant** 

#### **Specifications**

Face Nylon PBT Base Brass Contacts

Mounting Strap Galvanized steel Auto Self-grounding Staple Stainless steel Mounting Screws Zinc plated steel

## **Performance**

**Electrical** 

Current Interrupting Receptacle certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

**Environmental** 

UL 94V-2 Flammability

**Operating Temperature** Maximum continuous 75°C; minimum -40°C (without

impact)



#### Accessories

Wallplate or Weatherproof Cover Duplex Opening

#### Resources

eCatalog

