

## Straight Blade Devices

20 Amp, 125 Volt, 2-Pole, 3-Wire

# SNAPConnect<sup>®</sup> Extra Heavy Duty Receptacle

# HUBBELL

### Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Surge suppression, Tamper-Resistant, LED Indicator

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Surge Protection Receptacle	White	783585252087	SNAP5362WS

### Listings

UL Listed to UL498 File No. E2467  
Certified to CSA, C22.2, No. 42 File 566  
Fed. Spec. W-C-877  
NEMA<sup>®</sup> WD-6 Compliant

### Specifications


Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass

### Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device

<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)



### Complementary Products

Wallplate or Weatherproof Cover  
Opening

### Online Resources

Customer Sales Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

