

Straight Blade Devices

20A, 250V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty SNAPconnect® Single Receptacle



- Features
- Audible SNAP indicates solid connection
 - Reduces installation time
 - Fully insulated design

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|--|--------------|--------------|----------------|
| Specification grade, smooth nylon face | Gray | 783585531007 | SNAP5461GYTR |

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Specifications

| | |
|---------------------------------|-------------------|
| Face | Nylon |
| Base | Nylon |
| Power Contacts | Brass |
| Ground Contacts | Brass |
| Mounting Strap | Galvanized steel |
| Automatic Self-grounding Staple | Stainless steel |
| Mounting Screws | Zinc plated steel |

Performance

| | |
|------------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Flammability | UL 94V-2 |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (w/o impact) |
| Product Identification | Ratings are a permanent part of the device |



Complementary Products

| | |
|------------------------|-----------|
| Stranded SNAPconnector | SNAP252RA |
| Solid SNAPconnector | SNAP251RA |

Online Resources

eCatalog

