Straight Blade Devices

20 Amp, 125 Volt, 2-Pole, 3-Wire

SNAPConnect® Hospital Grade Receptacle

HUBBELL

Features

- · Audible SNAP, indicates solid connection
- · Reduces installation time
- · Tamper-Resistant, LED Indicator
- Assembled in USA

Ordering Information

DescriptionHospital Grade,
Tamper-Resistant, Hospital
Grade, Power Indicating LED

Device Color UPC Number Ivory 783585553511 Catalog Number SNAP8300ILTRA




Listings

UL Listed to UL498 File No. E2537 Certified to CSA, C22.2, No. 42 File 636 Fed. Spec. W-C-947 NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass



Performance

Electrical

Current Interrupting Certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

Environmental

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C; minimum -40°C

(without impact)

Complementary Products

Wallplate or Weatherproof Cover Opening

Online Resources

Customer Sales Drawing eCatalog

Installation Instructions

