

Temporary Power

Temporary Industrial Lighting

Fluorescent Maintenance Worklights

HUBBELL

Features

- Inline straight blade NEMA 5-15R tool tap keeps power away from users hands
- Bumpers and soft handle provide impact protection
- Tough polycarbonate outer tube and end lenses



Ordering Information

Description	UPC	Catalog Number
Fluorescent worklight with Twist-Lock plug and tool tap	783585494524	TW25F2

Standards

UL
CSA
ETL

Specifications

Light Type	Fluorescent
Outer Tube Material	Polycarbonate
Plug Type	Twist-Lock® L5-20P
Included	Steel Hook

Performance

Electrical	
Lumen Output	825
Rating	20A 125V
Tool Tap Capacity	12 Amps
Wattage	13

Mechanical	
Cord Length	25 ft.
Cord Type	16/3 SJTOW

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

