

Straight Blade Devices  
15A, 125V, 2 Pole, 3 Wire Grounding  
Acceptor® Hazardous Location Plugs

# HUBBELL

## Ordering Information

Description	Device Color	UPC	Catalog Number
Explosion and dust ignition proof, Male Plug, Single Pack	Metallic	783585412351	UGP15231



## Listings

Listed to UL Standard 498

## Resources

[eCatalog](#)

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

### Environmental

Flammability	UL 94 HB or better
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

