

Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding USB Charger Receptacles

HUBBELL

Features

- Switch Combo Outlets
- Two USB type 2.0 ports, 2.1 Amp, 5V DC
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

Ordering Information

Description	Device Color	UPC	Catalog Number
Switch Combo Outlet, two USB type 2.0 ports, 2.1 Amp, 5 Volt DC, Style Line® decorator.	White	883778305665	USB102W



Listings

cULus listed

Resources

eCatalog

Specifications

Face	RTP
Base	RTP
Mounting Screws	Zinc plated steel
Terminal Screws	Plated steel
USB Port	Stainless Steel

Performance

Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal

Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

