

Charging Solutions Power Charging Station

15A Combination Wireless Wall Mount Charger & USB Outlet

HUBBELL

Features

- Qi certified
- No need for cables
- Dual coils for optimum phone positioning
- Secure phone holder

Ordering Information

Description	Color	UPC Number	Catalog Number
Combination Wireless Wall Mount Charger & USB Outlet	White	883778309427	USB1518



Listings

cULus UL 1310, UL 498
FCC Part 15

Specifications

Face	Reinforced Thermoplastic
Base	Reinforced Thermoplastic
LED	Green/Blue Indicator
Terminal Screws	Plated Steel
Mounting Screws	Zinc Plated Steel

Performance

Electrical

Qi Rating	Certified 7.5 Watts
Input Voltage	125V
Dielectric Voltage	Withstands 1,500V minimum Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental Flammability

Operating Temperature	UL 94V-2 Maximum continuous 75°C, minimum -40°C (w/o impact)
-----------------------	---

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

