Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding USB Charger Duplex Receptacle

HUBBELL

Features

- High Power 3.1 Amp, 5 Volt USB Output
- · Two Type A USB Ports
- Tamper Resistant Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Ordering Information

Description Color
Tamper Resistant 15A/125V Black
Duplex, 3.1 Amp, 5 Volts
USB Ports

UPC Number 883778309908

Catalog Number

USB15ABK

Listings

cULus Listed to UL498, UL1310

Specifications

Mounting Strap

Face
Reinforce Thermoplastic
Base
Reinforce Thermoplastic
USB Port
Stainless Steel
Contacts
Clamp
Plated Steel
Terminal Screws

.040" Zinc Plated Steel
Reinforce Thermoplastic
Stainless Steel
Plated Steel
Plated Steel
Plated Steel

Performance

Mounting Screws

Electrical

Current Inturrupting Certified for current inturrupting at full rated current

Dielectric Voltage Withstands 1,500 V minimum

Complies with USB BC1.2 Battery Charging and 3.0

Power Delivery Specifications

Zinc Plated Steel

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor

only

Terminal Identification Terminals identified in accordance with UL 498 and

CSA

USB Ports Stainless steel rated for 10,000 plug insertions and

removal

Environmental

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o

impact)







