

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

USB-C Power Delivery (PD) Charging Receptacle

HUBBELL

Features

- USB-C PD Port Delivers up to 20V, 55W Output
- 2nd USB-A Port for Convenience Charging (1.5A, 5V)
- Tamper Resistant Commercial Grade Duplex Receptacle
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

Ordering Information

| Description | Color | UPC Number | Catalog Number |
|---|-------|--------------|----------------|
| Commercial Spec Grade, 15A/125V, TR Duplex, with (1) USB-C Power Delivery port with up to 55W output and (1) USB-Type A Convenience port 1.5A, 5V output, | Gray | 783585565910 | USB15ACPDGY |



Listings

cULus Listed to UL498, UL1310

Specifications

| | |
|----------------------|--|
| Face | Impact Resistant Thermoplastic |
| Base | RTP |
| Single LED Indicator | Power Indication (White)/USB Charging (Blue) |
| Contacts | Brass Triple-Wipe |
| Clamp | Plated Steel |
| Terminal Screws | Plated Steel |
| Mounting Strap | .040" Zinc Plated Steel |
| Mounting Screws | Zinc Plated Steel |
| USB Port | Stainless Steel |
| Auto-Ground Staple | Stainless Steel |

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Performance

| Electrical | |
|-------------------------|---|
| Current interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum, Complies with USB BC1.2 Battery Charging and 3.1 Power Delivery Specifications |
| Mechanical | |
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #14-#10 AWG copper stranded or solid conductor only |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |
| USB Ports | Stainless steel, rated for 10,000 charge-cable insertion cycles |
| Environmental | |
| Flammability | UL 94V-2 |
| Operating Temperature | Maximum continuous 75°C, minimum -40°C (w/o impact) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

