

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

USB Charger Receptacles

HUBBELL

Features

- High Power 5 Amp, 5 Volt USB Output
- Combination Ports, One Type A, One Type C
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Ordering Information

Description	Color	UPC Number	Catalog Number
Tamper Resistant 20A/125V Duplex, 5 Amp, 5 Volts USB Ports	Brown	883778307225	USB20AC5

Listings

cULus Listed to UL498, UL1310

Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Steel
Clamp	Plated Steel
Terminal Screws	Plated Steel
Mounting Strap	.040" Zinc Plated Steel
Mounting Screws	Zinc Plated Steel
USB Port	Stainless Steel



20A STANDARD
GRADE DEVICE

Online Resources

eCatalog

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Ports	Stainless steel rated for 10,000 plug insertions and removal
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)