

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

USB Charger Receptacles



Features

- Weather and Tamper Resistant Commercial Grade
- Two Type C USB Ports
- High Power 5 Amp, 5 Volt USB Output
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

Ordering Information

Description	Color	UPC Number	Catalog Number
Weather and Tamper Resistant 15A/125V Duplex, 5 Amp, 5 Volts USB Ports	Brown		USB20C5WR

Listings

cULus Listed to UL498, UL1310  
Complies with battery charging specification USB BC1.2  
Compatible with USB 1.1/2.0/3.0 devices, including Apple® products  
Meets Section 406.9 of the NEC making it suitable for outdoor use.

Specifications

Code Compliance	Complies with Part 15 of the FCC Rules
Electrical Ratings	15 or 20 Amp, 125V AC
Port Rating	5 Amp, 5 Volt
Indicator	Green LED
Contacts	Brass Triple-Wipe
Terminal Screws	Stainless Steel
Mounting Strap	Brass
Mounting Screws	Stainless Steel
USB Port	Stainless Steel
Auto-Ground Staple	Stainless Steel

Performance

<b>Electrical</b>	
Current Interrupting	Certified at full rated current
Dielectric Voltage	Withstands 1,500V minimum
<b>Mechanical</b>	
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)
Outdoor Suitability	UL 746C f1
USB Ports	Stainless steel, rated for 10,000 charge-cable insertion cycles
<b>Environmental</b>	
Flammability	UL 94V-2
Outdoor Suitability	UL 746C f1, Weather Resistant Device suitable for use outdoor with 3R extra duty protected enclosure, in compliance with NEC 406.9



20A WEATHER RESISTANT (WR) DEVICE

Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

