Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding USB Charger Receptacles

Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type C USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Ordering Information

DescriptionColorTamper Resistant 20A/125VWhiteDuplex, 5 Amp, 5 Volts USBPorts

UPC Number Catalog Number 883778307522 USB20C5W

Listings


cULus Listed to UL498, UL1310

Specifications

Face Base LED Contacts Clamp Terminal Screws Mounting Strap Mounting Screws USB Port RTP RTP Green Indicator Plated Steel Plated Steel Idted Steel .040" Zinc Plated Steel Zinc Plated Steel Stainless Steel



HUBBELL



Online Resources

eCatalog

Performance

Electrical	
Current Inturrupting	Certified for current inturrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Ports	Stainless steel rated for 10,000 plug incertions and removal
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

