

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

# USB-C Power Delivery (PD) Charging Receptacle

# HUBBELL

## Features

- USB-C PD Port Delivers up to 20V, 55W Output
- 2nd USB-C Port for Convenience Charging (1.5A, 5V)
- Tamper Resistant Commercial Grade Duplex Receptacle
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

## Ordering Information

| Description   | Color | UPC Number   | Catalog Number |
|---|-------|--------------|----------------|
| Commercial Spec Grade, 20A/125V, TR Duplex, with (1) USB-C Power Delivery port with up to 55W output and (1) USB-C Convenience port 1.5A, 5V output | Brown | 783585723211 | USB20CPD       |



## Listings

cULus Listed to UL498, UL1310

## Specifications

|                      |  |
|----------------------|--|
| Face                 | Impact Resistant Thermoplastic               |
| Base                 | RTP  |
| Single LED Indicator | Power Indication (White)/USB Charging (Blue) |
| Contacts             | Brass Triple-Wipe                            |
| Clamp                | Plated Steel                                 |
| Terminal Screws      | Plated Steel                                 |
| Mounting Strap       | .040" Zinc Plated Steel                      |
| Mounting Screws      | Zinc Plated Steel                            |
| USB Port             | Stainless Steel                              |
| Auto-Ground Staple   | Stainless Steel                              |

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

## Performance

### Electrical

|                      |   |
|----------------------|---|
| Current interrupting | Certified for current interrupting at full rated current  |
| Dielectric Voltage   | Withstands 2,000V minimum, Complies with USB BC1.2 Battery Charging and 3.1 Power Delivery Specifications |

### Mechanical

|                         |   |
|-------------------------|---|
| Product Identification  | Ratings are a permanent part of the device                      |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only             |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA          |
| USB Ports               | Stainless steel, rated for 10,000 charge-cable insertion cycles |

### Environmental

|                       |   |
|-----------------------|---|
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C, minimum -40°C (w/o impact) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

