

# Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding USB Charger Outlets

# HUBBELL

## Features

- Four USB ports 5 Amp, 2 Type A and 2 Type-C USB, 5V DC, class 2.0
- Fast charge enabled modulates up to 9 volts
- Switch activated port door; when open enables power; when closed, all power is switched off, for a “zero” no-load draw
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

## Ordering Information

Description	Device Color	UPC	Catalog Number
USB Charger 4 Port Outlet, 2 Type A, 2 Type-C USB Ports, 5 Amp, up to 9 Volt DC, Style Line Decorator	Gray	883778308956	USB4ACGY

## Listings

cULus  
FCC Approved  
Compatible with USB 1.1/2.0/3.0 Devices

## Specifications

Face	Reinforced Thermoplastic
Base	Reinforced Thermoplastic
LED	Green Indicator
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
Terminal Screws	Plated steel
USB Port	Stainless Steel

## Performance

<b>Electrical</b>	
Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum

<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal

<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



## Resources

Installation Instructions  
Sales Drawing  
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

