

# Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding USB Charger Outlets

# HUBBELL

## Features

- Four USB ports 5 Amp, 2 Type A and 2 Type-C USB, 5V DC, class 2.0
- Fast charge enabled modulates up to 9 volts
- Switch activated port door; when open enables power; when closed, all power is switched off, for a “zero” no-load draw
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

## Ordering Information

| Description   | Device Color | UPC          | Catalog Number |
|---|--------------|--------------|----------------|
| USB Charger 4 Port Outlet, 2 Type A, 2 Type-C USB Ports, 5 Amp, up to 9 Volt DC, Style Line Decorator | Ivory        | 883778308963 | USB4ACI        |

## Listings

cULus  
FCC Approved  
Compatible with USB 1.1/2.0/3.0 Devices

## Specifications

|                            |                          |
|----------------------------|--------------------------|
| Face                       | Reinforced Thermoplastic |
| Base                       | Reinforced Thermoplastic |
| LED                        | Green Indicator          |
| Mounting Strap             | Galvanized steel         |
| Auto Self-grounding staple | Stainless steel          |
| Mounting Screws            | Zinc plated steel        |
| Terminal Screws            | Plated steel             |
| USB Port                   | Stainless Steel          |

## Performance

|                      |   |
|----------------------|---|
| <b>Electrical</b>    |   |
| Current Interrupting | Receptacle certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 1,500V minimum   |

|                         |  |
|-------------------------|--|
| <b>Mechanical</b>       |  |
| Product Identification  | Ratings are a permanent part of the device                   |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only          |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA       |
| USB Port                | Stainless steel Rated for 10,000 plug insertions and removal |

|                       |   |
|-----------------------|---|
| <b>Environmental</b>  |   |
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (w/o impact) |



## Resources

Installation Instructions  
Sales Drawing  
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

