

Straight Blade Devices
125V, 2 Pole, 3 Wire Grounding
USB Charger Outlets

HUBBELL

Features

- Four USB ports 5 Amp, 2 Type A and 2 Type-C USB, 5V DC, class 2.0
- Fast charge enabled modulates up to 9 volts
- Switch activated port door; when open enables power; when closed, all power is switched off, for a “zero” no-load draw
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

Ordering Information

Description	Device Color	UPC	Catalog Number
USB Charger 4 Port Outlet. 2 Type A, 2 Type-C USB Ports. 5 Amp, up to 9 Volt DC, Style Line Decorator	Light Almond	883778308970	USB4ACLA

Listings

cULus
FCC Approved
Compatible with USB 1.1/2.0/3.0 Devices

Specifications

Face	Reinforced Thermoplastic
Base	Reinforced Thermoplastic
LED	Green Indicator
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
Terminal Screws	Plated steel
USB Port	Stainless Steel

Performance

Electrical	
Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Installation Instructions
Sales Drawing
eCatalog

