

## Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

# Hospital Grade USB-C Power Delivery (PD) Charging Receptacle

# HUBBELL

## Features

- USB-C PD Port Delivers up to 20V, 55W Output
- 2nd USB-A Port for Convenience Charging (1.5A, 5V)
- Tamper Resistant Hospital Grade Duplex Receptacle
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

## Ordering Information

Description	Color	UPC Number	Catalog Number
Hospital Grade, 15A/125V, TR Duplex, with (1) USB-C Power Delivery port with up to 55W output and (1) USB-Type A Convenience port 1.5A, 5V output,	White	783585723075	USB8200ACPDW



## Listings

cULus Listed to UL498, UL1310

## Specifications

Face	Impact Resistant Thermoplastic
Base	RTP
Single LED Indicator	Power Indication (White)/USB Charging (Blue)
Contacts	Brass Triple-Wipe
Clamp	Plated Steel
Terminal Screws	Plated Steel
Mounting Strap	.040" Zinc Plated Steel
Mounting Screws	Zinc Plated Steel
USB Port	Stainless Steel
Auto-Ground Staple	Stainless Steel

## Online Resources

eCatalog

## Performance

### Electrical

Current interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum. Complies with USB BC1.2 Battery Charging and 3.1 Power Delivery Specifications

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Ports	Stainless steel, rated for 10,000 charge-cable insertion cycles

### Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

