## Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hospital Grade USB Charger Receptacles

#### **Features**

- · High Power 5 Amp, 5 Volt USB Output
- Two Type A USB Ports
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

#### **Ordering Information**

**Description**Hopstial Grade, Tamper
Resistant 20A/125V Duplex,
5 Amp, 5 Volts USB Ports

UPC Number 883778307133 Catalog Number USB8300A5BK

### Listings

cULus Listed to UL498, UL1310

#### **Specifications**

Face RTP Base RTP

LED Green Indicator
Contacts Plated Steel
Clamp Plated Steel
Terminal Screws Plated Steel

Mounting Strap.040" Zinc Plated SteelMounting ScrewsZinc Plated SteelUSB PortStainless Steel

#### **Performance**

**Electrical** 

Current Inturrupting Certified for current inturrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Complies with USB BC1.2 Battery Charging and 3.0

Power Delivery Specifications

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor

only

Terminal Identification Terminals identified in accordance with UL 498 and

**CSA** 

USB Ports Stainless steel rated for 10,000 plug incertions and

removal

**Environmental** 

Flammability UL 94V-2


Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o

impact)

# HUBBELL



**GREEN DOT** 



20A HOSPITAL GRADE DEVICE

#### **Online Resources**

eCatalog

