

Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hospital Grade USB Charger Receptacles

HUBBELL

Features

- High Power 5 Amp, 5 Volt USB Output
- Combination Ports, One Type A, One Type C
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Ordering Information

Description	Color	UPC Number	Catalog Number
Hospital Grade, Tamper Resistant 20A/125V Duplex, 5 Amp, 5 Volts USB Ports	Gray	883778307409	USB8300AC5GY

Listings

cULus Listed to UL498, UL1310

Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Steel
Clamp	Plated Steel
Terminal Screws	Plated Steel
Mounting Strap	.040" Zinc Plated Steel
Mounting Screws	Zinc Plated Steel
USB Port	Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum
Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications

Mechanical

Product Identification Ratings are a permanent part of the device

Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only


Terminal Identification Terminals identified in accordance with UL 498 and CSA

USB Ports Stainless steel rated for 10,000 plug insertions and removal

Environmental

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o impact)



20A HOSPITAL
GRADE DEVICE

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

