# **Straight Blade Devices**

# 20A, 125V, 2 Pole, 3 Wire Grounding

# Hospital Grade USB-C Power Delivery (PD) Charging Receptacle

# HUBBELL

#### **Features**

- USB-C PD Port Delivers up to 20V, 55W Output
- 2nd USB-A Port for Convenience Charging (1.5A, 5V)
- Tamper Resistant Hospital Grade Duplex Receptacle
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

# **Ordering Information**

Description
Hospital Grade, 20A/125V,
TR Duplex, with (1) USB-C
Power Delivery port with up
to 55W output and (1)
USB-Type A Convenience
port 1.5A, 5V output,

Color Light Almond **UPC Number** 783585723129

Catalog Number USB8300ACPDLA



#### Listings

cULus Listed to UL498, UL1310

### **Specifications**

Single LED Indicator

Face Impact Resistant Thermoplastic

Base R<sup>-</sup>

Power Indication (White)/USB Charging

(Blue)

Contacts Brass Triple-Wipe
Clamp Plated Steel
Terminal Screws Plated Steel

Mounting Strap.040" Zinc Plated SteelMounting ScrewsZinc Plated SteelUSB PortStainless SteelAuto-Ground StapleStainless Steel

# **Online Resources**

Customer Sales Drawings

eCatalog

Installation Instructions

#### **Performance**

#### **Electrical**

Current interrupting Certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum, Complies with

USB BC1.2 Battery Charging and 3.1 Power

**Delivery Specifications** 

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #14-#10 AWG copper stranded or solid

conductor only

Terminal Identification Terminals identified in accordance with UL 498

and CSA

USB Ports Stainless steel, rated for 10,000 charge-cable

insertion cycles

**Environmental** 

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o

impact)

Dimensions in Inches (mm)

