## Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hospital Grade USB Charger Receptacles

- High Power 5 Amp, 5 Volt USB Output
- Two Type C USB Ports
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

### **Ordering Information**

Description Hopstial Grade, Tamper Resistant 20A/125V Duplex, 5 Amp, 5 Volts USB Ports

Color White **UPC Number** 883778307669 **Catalog Number** USB8300C5W

#### Listings

cULus Listed to UL498, UL1310

#### **Specifications**

Face **RTP** RTP Base

LED Green Indicator Plated Steel Contacts Plated Steel Clamp **Terminal Screws** Plated Steel

Mounting Strap .040" Zinc Plated Steel Mounting Screws Zinc Plated Steel **USB Port** Stainless Steel

#### **Performance**

**Electrical** 

**Current Inturrupting** Certified for current inturrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Complies with USB BC1.2 Battery Charging and 3.0

Power Delivery Specifications

Mechanical

**Product Identification** Ratings are a permanent part of the device #14-#10 AWG copper stranded or solid conductor **Terminal Accommodation** 

Terminal Identification Terminals identified in accordance with UL 498 and

**USB Ports** Stainless steel rated for 10,000 plug incertions and

removal

**Environmental** 

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o

# HUBBELL



#### GREEN DOT



20A HOSPITAL **GRADE DEVICE** 

#### **Online Resources**

eCatalog

