Sensing Devices

Passive Infrared

Wall Switch Sensors


HUBBELL

Features

- Nightlight version to provide illumination when the lights are OFF, neutral wire required
- Manual adjusting, manual ON operation
- Wallplate sold separately

Ordering Information

Description Manual adjusting, manual ON operation; 120V AC only **UPC Number** 783585428345 **Catalog Number** WS1025NI



Listings

cULus listed to UL 773A

Specifications

Flame retardant UL 94 V-0 ABS Housing

Polyethylene Lens

Face 2.59"H x 1.30"W, 0.61"D (from wall Dimensions

Mounting Height 73 to 54 inches above floor

Mounting Strap Steel

Complementary Products

Nylon Wallplate NP26I SS Wallplate **SS26** Snap-On Wallplate NPS26I

Online Resources

eCatalog

Performance

Controls

Front Press Switch ON/OFF

Service Switch OFF (service); ON (normal operation) Time Delay

6 seconds to 20 minutes (default set to 10 minutes)

Electrical

120VAC, 600W Incandescent, 5A Ballast, 5A Load Capacity

CFL/LED, 277V; Horsepower rating 1/6

Environmental

Operating Temperature 32°F to 122°F (0°C to 50°C) with rate of change not

exceeding 20°F(11°C) per hour

-40°F to 150°F (-40°C to 65°C); 20% to 90% non Storage

condensing relative humidity

Sensing Indicators

Passive Infrared Red LED

