H-MOSS® Controls Passive Infrared Wall Switches

HUBBELL

Features

- Designed for use on 120 or 277V AC circuits, no neutral required, fast retrofits. Built in photocell prevents lights from turning ON with sufficient natural light.
- 3-Way capable
- Matching wallplate included

Ordering Information

Description Manual adjusting; dual-voltage 120/277V; manual/auto ON operation

UPC Number Catalog Number 783585256856 WS2000LA

Listings

cULus listed to UL 773A

Specifications

Housing Flame retardant UL 94 V-0 ABS

Lens Polyethylene

Face 2.59"H x 1.30"W, 0.61"D (from wall out) **Dimensions**

Mounting Height 42 to 54 inches above floor

Mounting Strap Steel

Performance

Controls

Ambient Light Photocell, 10 to 500 foot candles

Service Switch OFF (service); vacancy (manual-ON); occupancy

(auto-ON)

Time Delay Manual 20 seconds to 30 minutes

Electrical

Load Capacity Incandescent - 0 to 1000 watts, 120V; Ballast - 0 to 1000

watts, 277V; Horsepower rating 1/6

Environmental

Operating Temperature 32°F to 122°F (0°C to 50°C) with rate of change not

exceeding 20°F(11°C) per hour

-40°F to 150°F (-40°C to 65°C); 20% to 90% non Storage


condensing relative humidity

Sensing Indicators

Passive Infrared Red LED







Complementary Products

SS Wallplate **SS26** Snap-On Wallplate RCW1LA

Online Resources

Customer Use Drawing

eCatalog

Installation Instructions

