

Switches

Heavy Duty

ScrubSwitch

HUBBELL

Features

- Designed to be sanitized with cleaning solutions
- 3R UL Rated - able to get wet
- 8 Amp 10 Amp 120/277 Volt SP and 3-Way
- ABS Smooth plastic plate

Ordering Information

Description	Color/Finish	UPC	Catalog Number
1 Gang, 3R rated switch, Single Pole and Three way, 8A 10A 120/277V with ABS Cover Plate	White Cover	783585723426	WSS1277PW

Listings

UL 60730-1 3R
CSA E60730-1

Specifications

Operating Temperature	32-104 degree F
Flammability	UL 94-2
Power Supply	120/277V AC, 50/60Hz
Switching Cycles	50000
Impact Resistance	UL746C, 5 lb withstand
Endurance	50K Cycles
Chemical Resistance	Ammonium chloride, Isopropanol, hydrogen peroxide, sodium hypochlorite



Related Products

Cover Plate

WSS1PW

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

