



ACC-F4-90-1, Stainless Steel Wire Management Clip, Dual Degree, 1 to 4 PV Wires, Module

By WILEY
Catalog # [ACC-F4-90-1](#)



90 Degree Module Cable Clip.

Application

1 to 4 PV cables
Wire Diameter Range: 4.1mm - 6.7mm per each cable

General

Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree & Straight on Flange Thickness Range: 1.3mm - 2.5 mm
Trade Name	WILEY
Type	Cable Clips
UPC	781810671351
UPC 12 Digit	7818106713511

Dimensions

Dimension - Length Overall inch	1.36 in
Dimension - Thread Size	-

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	4000
-----------------	------

Product Assets

[Catalogs - Wiley_WireManagementSolutions_Cat](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50042750](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WLY-ACC-F4-90-1-SPEC-EN | REV 1/2024