



ACC-FPV90, Stainless Steel, 90 degree, 2 wire Module Cable Clip

By WILEY
Catalog # ACC-FPV90



2 wire Module Cable Clip 90 Degree

Application

1 to 2 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable

General

Construction Material - Main	304 STAINLESS STEEL
EU RoHS Indicator	Under Review
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree, Flange Thickness Range: 1.0mm - 3.0mm
Sub Brand	Clip
Type	Cable clip
UPC	621945514508

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

Product Assets

[Catalogs - Wiley_WireManagementSolutions_Cat](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50084791](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WLY-ACC-FPV90-SPEC-EN | REV 1/2024