

ACC-F2-90, Stainless Steel Wire Management Clip, Dual Degree, 1 to 2 PV Wires, Module

By WILEY
 Catalog # [ACC-F2-90](#)



Wire Management Clip; For 1 or 2 USE-2 or PV Wires; Clips To Module.

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

General

Application	1 to 2 PV wires, Micro Inverter Trunk or AC cables, Wire Diameter Range: 6.24mm - 8.0mm per each cable (2 cables) 6.2mm - 14mm per each cable (1 cable)
Catalog Number	ACC-F2-90
Construction Material - Main	Nylon
EU RoHS Indicator	Contact Manufacturer
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree & Straight on Flange Thickness Range: 1.3mm - 2.5 mm
Trade Name	WILEY
Type	Cable Clips
UPC	781810671368
UPC 12 Digit	7818106713688

Dimensions

Dimension - Length Overall inch	0.452 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	4000
-----------------	------

Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50042747](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-ACCF290-SPEC-EN | REV 6/2024