



ACC-F4-90-1, Stainless Steel Wire Management Clip, Dual Degree, 1 to 4 PV Wires, Module

By WILEY
Catalog # [ACC-F4-90-1](#)



90 Degree Module Cable Clip.

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

General

Application	1 to 4 PV cables Wire Diameter Range: 4.1mm - 6.7mm per each cable
Catalog Number	ACC-F4-90-1
Item Type	3B
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree & Straight on Flange Thickness Range: 1.3mm - 2.5 mm
Trade Name	WILEY
Type	Cable Clips
UPC	781810671351
UPC 12 Digit	7818106713511

Dimensions

Dimension - Length Overall inch	1.36 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity 4000

Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50042750](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-ACCF4901-SPEC-EN | REV 6/2024