



ACC-F4F, Stainless Steel, 90 degree, 4 Wire Module Cable Clip

By WILEY
Catalog # [ACC-F4F](#)



4 wire Module Cable Clip 90 Degree

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

General

Application	1 to 4 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable
Catalog Number	ACC-F4F
Construction Material - Main Material	304 STAINLESS STEEL 304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree Flange Thickness Range: 1.0mm - 3.0mm
Sub Brand	Clip
Type	Cable clip
UPC	621945514515

Certifications And Compliance

Certification - CSA Approved	Y
Certification - cULus	Yes
Certified Listed	UL1565 Listed
Industry Standard(s)	UL 1565 Listed
UL Listed	Yes

Logistics

Minimum Pack Quantity 1000

Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Sales Drawings - 50085925](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-ACCF4F-SPEC-EN | REV 6/2024