



ACC-FPV, Stainless Steel Wire Management Clip, Straight on, 1-2 PV Wires, Module

By WILEY
Catalog # ACC-FPV



Wiley Management Clip; 1 or 2 PV Wires; 304 Stainless Steel;
Accommodates: PV Wire 5mm - 8 mm (dia.); Module Thickness:
1.0mm - 3 mm.

Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

General

Application	1 to 2 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable
Catalog Number	ACC-FPV
Construction Material - Main	Nylon
EU RoHS Indicator	Contact Manufacturer
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - Straight on Flange Thickness Range: 1.0mm - 3.0mm
Type	Cable Clips
UPC	621945472938

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
UL Listed	Yes

Logistics

Carton Quantity 5000

Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Sales Drawings - 50068480](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-ACCFPV-SPEC-EN | REV 6/2024