



# ACC-FPV180, Stainless Steel, 180 degree, 2 wire Module Cable Clip

By WILEY  
Catalog # [ACC-FPV180](#)



180 Degree Module Cable Clip.

## Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

## General

Application	1 to 2 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable
Catalog Number	ACC-FPV180
Construction Material - Main	Nylon
EU RoHS Indicator	Contact Manufacturer
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 180 Degree Flange Thickness Range: 1.0mm - 3.0mm
Sub Brand	Wiley
Type	Cable Clips
UPC	621945487956

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
UL Listed	Yes

## Logistics

Carton Quantity	4000
Minimum Pack Quantity	1000

## Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50076889](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WLY-ACCFPV180-SPEC-EN | REV 6/2024