



WEEB-BNDJMP18-AS, WEEB® Bonding Jumper, 18" with 1/4" Mounting hardware included, Assembled

By WILEY
Catalog # [WEEB-BNDJMP18-AS](#)

18" Bonding Jumper Braid Assembly.

Features

- UL 467 Listed, UL 2703 Listed
- Corrosion resistant, reliability for use throughout the lifetime of the PV system
- Equivalent to #6 AWG copper wire
- Available with or without WEEB washer technology, assembled or unassembled, with or without hardware
- In-stock standard lengths from 6" to 36", custom lengths available upon request

Application

WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal component that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

General



Catalog Number	WEEB-BNDJMP18-AS
Item Type	4D
Trade Name	WILEY
UPC	621945431034
UPC 14 Digit GTIN	006219454310344

Dimensions

Bolt Size	1/4 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - WEEBBNDJMP18AS](#)



A Hubbell brand