



WEEB-BNDJMP36, WEEB® Bonding Jumper, 1/4" Mounting hardware NOT included

By WILEY
Catalog # [WEEB-BNDJMP36](#)



WEEB® Bonding Jumper; 36" Tin Plated Braid with WEEB® Washer Technology.

General

Application
WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal component that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

Catalog Number WEEB-BNDJMP36
Item Type 4D
UPC 781810652091
UPC 12 Digit 7818106520911

Dimensions

Bolt Size 1/4 in
Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved N
Certification - ETL Y
Certification - UL Recognized N
Certification - cULus N
Certified Listed UL2703
Industry Standard(s) UL2703
Standards - RoHS Compliance Status CM
UL Listed Yes

Logistics

Carton Quantity 25
Pallet Quantity 4200

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50028019](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WEEBBNDJMP36-SPEC-EN | REV 6/2024