



WEEB-BNDJMP8.0, WEEB® Bonding Jumper, 6", M8 or 5/16" hardware NOT included

By WILEY
Catalog # [WEEB-BNDJMP8.0](#)



WEEB® Bonding Jumper.

General

Application WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal component that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

Catalog Number WEEB-BNDJMP8.0
Item Type 3B
UPC 781810537398
UPC 12 Digit 7818105373988

Dimensions

Bolt Size 5/16 in
Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	400
Pallet Quantity	2000

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Certifications - Certificate of Compliance, UL 2703](#)
[Certifications - UL Certificate of Compliance, UL 2703](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50002064](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WEEBBNDJMP80-SPEC-EN | REV 6/2024