



# WEEB-BNDJMP8.0AS, WEEB® Bonding Jumper, 6" with M8 or 5/16" hardware included

By WILEY  
Catalog # [WEEB-BNDJMP8.0AS](#)



Cu Bonding Jumper, 6.00 IN L, 0.315 IN Hole Dia.

## General

**Application**

WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal component that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

**Catalog Number** WEEB-BNDJMP8.0AS  
**Item Type** 3C  
**UPC** 781810565599  
**UPC 12 Digit** 7818105655999

## Dimensions

**Bolt Size** 5/16 in  
**Dimension - Thread Size** -

## Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	100
Pallet Quantity	7200

## Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)  
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50032943](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WLY-WEEBBNDJMP80AS-SPEC-EN | REV 6/2024