



WEEB-DSK12, 1.39" WEEB disk washer, Bottom Mount Application, 0.51" hole size

By WILEY
Catalog # [WEEB-DSK12](#)



WEEB® Washer Electrical Equipment Bond.

Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

General

Application	WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.
Catalog Number	WEEB-DSK12
Item Type	4D
Material	Stainless Steel
Trade Name	WILEY
UPC	781810644690
UPC 12 Digit	7818106446900

Dimensions

Dimension - Inside Diameter inch	13.10 in
Dimension - Outside Diameter inch	30.32 in
Dimension - Pad Width inch	30.64 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - ETL	Y
Certification - UL Recognized	Y
Certified Listed	UL2703 Recognized
Industry Standard(s)	UL2703 Recognized
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6000
Pallet Quantity	100

Product Assets

- [Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50017067](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WEEBDSK12-SPEC-EN | REV 6/2024