



WEEB-KSR, WEEB Top Clamp Washer, 1.39 IN L, 0.99 IN W , 0.31 IN hole size, Slotted+

By WILEY
Catalog # [WEEB-KSR](#)



304 Stainless Steel Electrical Equipment Bond Washer; 1.39" Length; 0.99" Width; 0.10" Height; .31" Hole; Slotted.

Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

General

Application	WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.
Catalog Number	WEEB-KSR
Item Type	4D
Material	304 Stainless Steel
UPC	781810537527
UPC 12 Digit	7818105375277

Dimensions

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL467 Recognized
Industry Standard(s)	UL467 Recognized
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	6000
-----------------	------

Product Assets

- [Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50001980](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WEEBKSR-SPEC-EN | REV 6/2024