



# WEEB-OCR, WEEB Top Clamp Washer, 1.36 IN L, 1.16 IN W , 0.33 IN hole size, Slotted

By WILEY  
Catalog # [WEEB-OCR](#)



304 Stainless Steel Electrical Equipment Bond Washer; 1.36" Length; 1.16" Width; 0.12" Height; 0.33" Hole Size; Slotted.

### Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

### General

Application	WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.
Catalog Number	WEEB-OCR
Item Type	4D
Material	304 Stainless Steel
UPC	781810544532
UPC 12 Digit	7818105445322

### Dimensions

Dimension - Thread Size -

### Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL2703 Recognized
Industry Standard(s)	UL2703 Recognized
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	6000
-----------------	------

### Product Assets

- [Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50008337](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WLY-WEEBOCR-SPEC-EN | REV 6/2024