



## WILEYBRAID10-916, Cu Braid, 10.00 IN L, 1.20 IN W, M14 or 9/16" Hardware NOT included

By WILEY  
Catalog # [WILEYBRAID10-916](#)



WILEY Bonding Jumpers are perfect for tracker applications, galvanized steel, or anywhere a WEEB® washer is not required.

### Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

### General

UPC 621945469075

### Dimensions

Bolt Size 9/16 in

### Certifications and Compliance

Certified Listed	UL2703
Industry Standard(s)	UL2703
UL Listed	Yes

### Logistics

Carton Quantity	100
Pallet Quantity	16800

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50070213](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WLY-WILEYBRAID10-916-SPEC-EN | REV 1/2024