



WILEYBRAID36, Cu Braid , 36.00 IN L, 0.709 IN W, M6 or 1/4" Hardware NOT included

By WILEY
Catalog # [WILEYBRAID36](#)

Wiley Braid; 36" Tin Plated.



General

Application The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

Catalog Number WILEYBRAID36

Item Type 3C

Trade Name WILEY

UPC 781810565636

UPC 12 Digit 7818105656366

Dimensions

Bolt Size 1/4 in

Dimension - Thread Size -

Certifications And Compliance

Certification - CSA Approved N

Certification - ETL Y

Certification - UL Recognized N

Certification - cULus N

Certified Listed UL2703

Industry Standard(s) UL2703

Standards - RoHS Compliance Status CM

UL Listed Yes

Logistics

Carton Quantity 25

Pallet Quantity 4200

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)

[Certifications - UL Certificate of Compliance, UL 2703](#)

[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - 50028922](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WILEYBRAID36-SPEC-EN | REV 6/2024