



WILEYBRAID6-516, Cu Braid, 6.00 IN L, 0.709 IN W, M8 or 5/16" Hardware NOT included

By WILEY
Catalog # [WILEYBRAID6-516](#)

WILEY Bonding Jumpers are perfect for tracker applications, galvanized steel, or anywhere a WEEB® washer is not required.



General

Application	The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.
Catalog Number	WILEYBRAID6-516
Item Type	3B
Trade Name	WILEY
UPC	621945448407
UPC 12 Digit	6219454484077

Dimensions

Bolt Size	5/16 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - ETL	Y
Certified Listed	UL2703
Industry Standard(s)	UL2703
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	10500

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Certifications - UL Certificate of Compliance, UL 2703](#)
- [Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50060537](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY-WILEYBRAID6516-SPEC-EN | REV 6/2024