



WBS10V, Cable/Wire Bundle Strap, 10 inch Long, 19-74 Mm Bundle Dia, 100 Lb (444 N) Load Rating, Crimpable Ferrule

By WILEY
Catalog # [WBS10V](#)



Cable/Wire Bundle Strap Type 2, 10 inch Long, 19-74 Mm Bundle Dia, 100 Lb (444 N) Load Rating.

General

Application	Bundles of PV wire, Micro Inverter Trunk or AC cable
Catalog Number	WBS10V
EU RoHS Indicator	Contact Manufacturer
Item Type	3B
Material	304 SS ferrule and SS wire with UV rated vinyl jacketing
Mounting Method	Crimped in the field with electrician linesman pliers or standard wire cutters
Tensile Strength	100 lb.
Trade Name	WILEY
Type	Cable Clips
UPC	621945453999
UPC 12 Digit	6219454539999

Dimensions

Dimension - Thread Size	-
Length	10 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL62275
Industry Standard(s)	UL62275
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Pallet Quantity	5000

Product Assets

- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - Certificate of Compliance, UL 62275, CSA C22.2 No. 62275](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50054219](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WLY_CA-WBS10V-SPEC-EN | REV 6/2024