



WILEYBRAID24-38, tresse en cuivre, 24.00 IN L, 0.87 IN W, M10 ou 3/8" Matériel NON inclus

Par WILEY

No de catalogue [WILEYBRAID24-38](#)

Les cavaliers de liaison WILEY sont parfaits pour les applications sur rail, l'acier galvanisé, ou partout où une rondelle WEEB® n'est pas nécessaire.

Général

Numéro de catalogue WILEYBRAID24-38
CUP 621945460980

Dimensions

Taille du boulon 3/8 in

Certifications et conformité

Liste certifiée UL2703
Norme(s) industrielle(s) UL2703
Répertorié UL Oui

Logistique

Quantité de cartons 50
Quantité de palettes 8400



Documentation

[Avis aux clients - Prop 65 Notice](#)
[Catalogues - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogues - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Certifications - UL Certificate of Compliance, UL 2703](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Dessins de vente - 50061796](#)
[Spécifications - WILEYBRAID24-38](#)
[Spécifications - WILEYBRAID24-38](#)



Une marque Hubbell

©2024 Hubbell Incorporated. Tous droits réservés
WLY_CA-WILEYBRAID2438-SPEC-FR | REV 7/2024