

Ground Fault Products

Commercial Standard Hospital Grade GFCI Receptacles

HUBBELL

Features

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Ordering Information

| Description | Color | UPC | Catalog Number |
|--------------------------------------------------------------------------------------------------------------------------------------|-------|-------------|----------------|
| 15A, 125V, Style Line®, hospital grade, AUTOGUARD® self test GFCI receptacle, flush face, back and side wired, multiple drive screws | Brown | 88377899915 | GFR82 |

Listings

UL Listed - Canadian and U.S.
Meets ADA Standards
Meets all NEC® requirements
CSA Certified
NEMA® WD-6 Compliant

Specifications

| | |
|-----------------|-------------------|
| Face | Nylon |
| Base | Nylon |
| Power Contacts | Brass |
| Ground Contacts | Brass |
| Mounting Strap | Brass |
| Mounting Screws | Zinc plated steel |

Performance

Electrical

| | |
|-------------------------------|----------------------------------------------------------|
| Amperage | 15A, 20A Feed Thru |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 1,500V minimum |
| Frequency | 60 Hz |
| Maximum Interrupting Capacity | 10,000A |
| Trip Level | 4 to 6 mA |
| Trip Time | .025 second nominal |
| Voltage | 120V AC +10% - 15% (102V to 132V) |

Mechanical

| | |
|-------------------------|--------------------------------------------------------|
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #14-#10 AWG copper stranded or solid conductor only |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

Environmental

| | |
|-----------------------|---------------------------------|
| Flammability | UL 94V-2 |
| Operating Temperature | -35°C to 66°C or -30°F to 150°F |



Related Products

Wallplates for duplex openings

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

