

Screwless Terminated InsulGrip® Flanged Receptacle**Features**

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

Ordering Information

Description	UPC	Catalog Number
Nylon casing, back wired	78358571923	HBL2526ST

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Housing	Nylon
Terminal Retainer	Nylon
Plunger	Nylon
Contacts	Brass
Terminal Spring Clamp	Spring Steel
Assembly Screws	Zinc Plated Tri-drive
Weight (lbs)	0.4

Performance**Electrical**

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 3,000V minimum

Mechanical

Terminal Accommodation	#14 AWG - #10 AWG solid or #14 AWG - #8 AWG stranded copper wire
Terminal Identification	Terminals identified in accordance with UL 507

Environmental

Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)

**Online Resources**

Customer Sales Drawings
eCatalog
Installation Instructions